

## Product data sheet

### Characteristics

# 1025USBC-WC

## Double Switch Power Point, Clipsal Solis T Series, with USB C Charger, Horizontal Mount, 230V-240V, 10A



### Main

Product or component type	Switched socket with USB charger
Assembly Type	Complete product
Standards	AS/NZS 3112
Product certifications	RCM
Main colour tint	White ceramic

### Complementary

Range	Clipsal Solis T Series
Number Of Outlets	2
Device mounting	Wall mounted 65 mm
Cover type	With shutter
Number of power socket outlets	2 x 2P + E, Australian/New Zealand
Rated current	10 A 230/240 V, AC, 50 Hz
Connections - terminals	4 x 2.5 mm <sup>2</sup> screw terminals 3 x 4 mm <sup>2</sup> screw terminals
Colour tint	White ceramic
Surface finish	Polished ceramic
Surface treatment	Polished
Additional Function	USB type C
Material	Ceramic
Screwdriver shape	Philips No 2 Square drive no 1 (SQ1)
Wire stripping length	16 mm
Fixing mode	By screw
Fixing center	120 mm
Height	74 mm
Width	148 mm
Depth	68.9 mm
Sale per indivisible quantity	1
Installation Type	Flush
Installation Orientation	Horizontal
Control type	Rocker
Cover Thickness	3.9 mm
Cut-out dimensions	130 x 50 mm
Number Of Switches	2

## Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	8 cm
Package 1 Length	8 cm
Package 1 Weight	287 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	32.5 cm
Package 2 Width	25 cm
Package 2 Length	41 cm
Package 2 Weight	8.99 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations