

Product data sheet

Characteristics

1025XUA-WC

Double Switch Power Point, Clipsal Solis T Series, Horizontal Mount, 230V-240V, 10A, Removable Extra Switch



Main

Range	Clipsal Solis T Series
Product or component type	Switched socket
Product brand	Clipsal
Assembly Type	Complete product
Colour tint	White ceramic
Protection	Shuttered
Main colour tint	White ceramic

Complementary

Control type	Rocker
Number Of Outlets	2
Socket-outlet type	Double socket-outlet
Mounting Type	Screw
Installation Type	Flush
Installation Orientation	Horizontal
Material	Ceramic
Surface finish	Polished
[Ue] rated operational voltage	230/240 V AC
Network frequency	50 Hz
[In] rated current	10 A
Connections - terminals	4 x 2.5 mm ² screw terminals 3 x 4 mm ² screw terminals
Embedding depth	23.5 mm
Depth	27.4 mm
Height	74 mm
Width	148 mm
Mounting Centers	120 mm
Cut-out dimensions	130 x 50 mm
Surface treatment	Painted
Screwdriver shape	Philips No 2 Square drive no 1 (SQ1)
Wire stripping length	16 mm
Number of power socket outlets	2 x 2P + E, Australian/New Zealand
Cover Thickness	5 mm
Number Of Switches	2

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Product certifications	RCM
Standards	AS/NZS 3112
Relative humidity	10...95 %
Ambient air temperature for operation	0...45 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	6 cm
Package 1 Length	8 cm
Package 1 Weight	202 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	32.5 cm
Package 2 Width	25 cm
Package 2 Length	41 cm
Package 2 Weight	8.46 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations