

## Product data sheet

### Characteristics

# 1043TA-WC

## Flush Switch, Clipsal Solis T Series, Horizontal Mount, 3 Gang, 230V-240V, 10AX 1-Way/2-Way

### Main

Range	Clipsal Solis T Series
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Complete product
Outlet standard deviation	Australian/New Zealand
Colour tint	White ceramic

### Complementary

Number of gangs	3 gangs
[Ue] rated operational voltage	230/240 V
Network type	AC
Network frequency	50 Hz
Rated current	20 A/16 AX
Control type	Toggle switch
Connections - terminals	Screw terminals
Installation Type	Flush
Number Of Switches	3
Material	Ceramic
Installation direction	Horizontal
Surface treatment	Polished
Load type	LEDi lamp 0...250 W 20 A/16 AX
Terminals Capacity	4 x 1.5...3 x 2.5 mm <sup>2</sup>
Screwdriver shape	Philips No 2 Square drive no 1 (SQ1)
Wire stripping length	10 mm
Mounting Type	Screw
Cover Thickness	3.6 mm
Mounting Centers	84 mm
Cut-out dimensions	93 x 50 mm
Product certifications	RCM
Surface finish	Polished
Height	74 mm
Width	148 mm
Depth	56 mm
Embedding depth	41 mm
Motor M-rating AS3133	M80
Switch function	1-pole 1/2-way

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 60669

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	8 cm
Package 1 Length	8 cm
Package 1 Weight	166 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	34 cm
Package 2 Width	36 cm
Package 2 Length	48 cm
Package 2 Weight	5.064 kg

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	2