

Product data sheet

Characteristics

10DS-WE

SOCKET AUTO SWITCHED SINGLE DOUBLE POLE 10A WITH SAFETY SHUTTER



Main

Range of product	Standard Series
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate

Complementary

Colour code	WE
Marking	Without marking
Protection type	Fingersafe
Local signalling	Without light indicator
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	16 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm
Number of poles	2

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.08 kg
Package 1 Height	16 mm
Package 1 width	73 mm
Package 1 Length	115 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.4 kg
Package 2 Height	117 mm
Package 2 width	102 mm

Package 2 Length	138 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	4 kg
Package 3 Height	157 mm
Package 3 width	305 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile