

Product data sheet

Characteristics

10MD15S-WE

SWITCHED SOCKET MECHANISM DOUBLE POLE 15A SHUTTER



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Protection type	Fingersafe
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Depth	29 mm
Length	97 mm
Width	43 mm
Fixing center	84 mm
Number of poles	2

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	4.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	57 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	8.2 cm
Package 2 Width	17.5 cm
Package 2 Length	27.1 cm

Package 2 Weight	320 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	25 cm
Package 3 Width	21.4 cm
Package 3 Length	33.8 cm
Package 3 Weight	6.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile