

## Product data sheet

### Characteristics

# 10MDS-WE

## SWITCHED SOCKET MECHANISM DOUBLE POLE 10A SHUTTER



### Main

Range of product	Standard Series
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Protection type	Fingersafe
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	33 mm
Length	60 mm
Width	42 mm
Fixing center	50 mm
Number of poles	2

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg
Package 1 Height	3.3 cm
Package 1 width	4.2 cm
Package 1 Length	6 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Weight	100.0 kg
Package 2 Height	25 cm
Package 2 width	21.4 cm

Package 2 Length	33.8 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	5.0 kg
Package 3 Height	7 cm
Package 3 width	9.2 cm
Package 3 Length	11.8 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>