

Product data sheet

Characteristics

10MLB-WE

SWITCHED SOCKET MECHANISM LESS BRACKET



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	29 mm
Length	97 mm
Width	43 mm
Fixing center	84 mm
Number of poles	1

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.052 kg
Package 1 Height	2.9 cm
Package 1 width	4.3 cm
Package 1 Length	9.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.26 kg
Package 2 Height	68 mm
Package 2 width	84 mm
Package 2 Length	108 mm

Unit Type of Package 3	CAR
Number of Units in Package 3	125
Package 3 Weight	6.5 kg
Package 3 Height	250 mm
Package 3 width	214 mm
Package 3 Length	338 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile