

## Product data sheet

### Characteristics

# 11/2-WE

## TWIN SWITCHED SOCKET



### Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 2
Cover type	Full cover plate

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Mounting support	skirt
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	17 mm
Length	125 mm
Width	50 mm
Fixing center	104 mm
Number of poles	1

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.132 kg
Package 1 Height	17 mm
Package 1 width	50 mm
Package 1 Length	125 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.676 kg
Package 2 Height	108 mm
Package 2 width	110 mm
Package 2 Length	154 mm
Unit Type of Package 3	CAR

Number of Units in Package 3	50
Package 3 Weight	6.6 kg
Package 3 Height	250 mm
Package 3 width	214 mm
Package 3 Length	338 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>