

Product data sheet

Characteristics

1131115

Thorsman installation material, nail plug with screw, 5 x 50 mm



Main

| | |
|---------------------------|--|
| Range of product | Thorsman |
| Product or component type | Nail plug |
| Product name | Thorsman THI |
| Device short name | THI |
| Provided equipment | Screw |
| Device application | High load installation in board material |

Complementary

| | |
|---------------------------------------|---|
| Colour tint | Transparent |
| Practical load capacity | Pull-out load: 350 N for concrete B25 Pull-out load: 250 N for brick Pull-out load: 200 N for sandstone |
| Practical load capacity | Pull-out load: 35 kg for concrete B25 Pull-out load: 25 kg for brick Pull-out load: 20 kg for sandstone |
| Ambient air temperature for operation | -40...70 °C |
| Diameter | 5 mm |
| Length | 50 mm |



Environment

| | |
|-------------------------------|------------|
| Quantity per set | Set of 100 |
| Sale per indivisible quantity | 100 |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.7 cm |
| Package 1 Width | 0.7 cm |
| Package 1 Length | 7.3 cm |
| Package 1 Weight | 4 g |

Offer Sustainability

| | |
|--------------------------|--|
| Sustainable offer status | Green Premium product |
| RECh Regulation |  RECh Declaration |
| RECh free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |

| | |
|----------------------------|---|
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
