

Product data sheet

Characteristics

1131130

Thorsman THI - hammer fixing with screw - 6 x 35 mm



Main

Range of product	Thorsman
Product or component type	Hammer fixing
Product name	Thorsman THI
Device short name	THI
Provided equipment	Screw
Device application	High load installation in board material

Complementary

Colour tint	Transparent
Practical load capacity	Pull-out load: 500 N for concrete B25 Pull-out load: 400 N for brick Pull-out load: 300 N for sandstone
Practical load capacity	Pull-out load: 50 kg for concrete B25 Pull-out load: 40 kg for brick Pull-out load: 30 kg for sandstone
Ambient air temperature for operation	-40...70 °C
Diameter	6 mm
Length	35 mm



Environment

Quantity per set	Set of 100
Sale per indivisible quantity	100

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.0 g
Package 1 Height	0.8 cm
Package 1 width	0.8 cm
Package 1 Length	6.4 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
