

Product data sheet

Characteristics

1131145

Thorsman installation material, nail plug with screw, 6 x 70 mm



Main

Range of product	Thorsman
Product or component type	Hammer fixing
Product name	Thorsman THI
Device short name	THI
Provided equipment	Screw
Device application	High load installation in board material

Complementary

Colour tint	Transparent
Practical load capacity	Pull-out load: 500 N for concrete B25 Pull-out load: 400 N for brick Pull-out load: 300 N for sandstone
Practical load capacity	Pull-out load: 50 kg for concrete B25 Pull-out load: 40 kg for brick Pull-out load: 30 kg for sandstone
Ambient air temperature for operation	-40...70 °C
Diameter	6 mm
Length	70 mm



Environment

Quantity per set	Set of 100
Sale per indivisible quantity	100

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	0.8 cm
Package 1 Length	9.7 cm
Package 1 Weight	7 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
