

## Product data sheet

### Characteristics

# 1206028

## Cavity Fixing, Thorsman, TMM 8x26, without screw, set of 100



### Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TMM
Provided equipment	Without screw
Device application	3...26 mm lightweight installation in plasterboard
Colour tint	White
Quantity per set	Set of 100

### Complementary

Mounting support	Wall mounted
Drilling diameter	8 mm
Material	PA (polyamide)
Practical load capacity	0.2 kN shear 0.06 kN pull-out load
Length	26 mm
Width	13 mm
Height	16 mm
Net weight	0.0009 kg

### Environment

Ambient air temperature for operation	-40...80 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	1.3 cm
Package 1 Length	2.6 cm
Package 1 Weight	0.731 g

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

---

Warranty

18 months

---