


## Product data sheet

### Characteristics

# 1208057

## Thorsman installation material, TOG, M5x50 mm, cavity fixing spring toggle, set of 50



### Main

Range of product	Thorsman
Product or component type	Cavity fixing
Product name	Thorsman TOG
Device short name	TOG
Provided equipment	Screw
Mounting support	Board material
Device application	Board material
Mounting support	Wall mounted
Thread type	M5
Screw diameter	5 mm
Screw length	50 mm
Drilling diameter	14 mm
Colour tint	Metal

### Complementary

Quantity per set	Set of 50
Sale per indivisible quantity	50

### Environment

Material	Screw: steel electroplated Cavity fixing: sheet metal electroplated
Practical load capacity	Pull-out load: 180 N for 13 mm plasterboard
Thickness	0...20 mm fixture
Environmental characteristic	Fire resistance

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.1 cm
Package 1 Width	4.8 cm
Package 1 Length	6 cm
Package 1 Weight	11.9 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	8.5 cm
Package 2 Width	8.5 cm
Package 2 Length	10.6 cm
Package 2 Weight	643 g
Unit Type of Package 3	CAR
Number of Units in Package 3	900
Package 3 Height	13.5 cm
Package 3 Width	27 cm

Package 3 Length	55 cm
Package 3 Weight	12.22 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>