

Product data sheet

Characteristics

1220010

Thorsman - TPD-VS - cavity fixing - without screw - set of 100



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TPD-VS
Provided equipment	Without screw
Device application	9 mm lightweight installation in plasterboard
Colour tint	White
Quantity per set	Set of 100

Complementary

Mounting support	Wall mounted
Material	PA (polyamide) Glass fibre reinforced
Practical load capacity	0.19 kN shear 13 mm board 0.5 kN pull-out load 13 mm board
Thickness	0...12 mm fixture
Diameter	13 mm
Length	37 mm
Product weight	0.177 kg

Environment

Ambient air temperature for operation	-40...80 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.2 g
Package 1 Height	4 cm
Package 1 width	1.4 cm
Package 1 Length	3.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Weight	412 g
Package 2 Height	8 cm
Package 2 width	8.4 cm
Package 2 Length	14.8 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	2000
Package 3 Weight	8.888 kg
Package 3 Height	18.6 cm
Package 3 width	31.4 cm
Package 3 Length	43.4 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------