

Product data sheet

Characteristics

1220104

Thorsman installation material, TPD, cavity fixing, with screw, set of 100



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Product name	Thorsman TPD
Device short name	TPD
Provided equipment	Screw
Mounting support	Board material
Device application	Board material
Mounting support	Wall mounted
Screw diameter	4.5 mm
Screw length	35 mm
Size of screw head	8 mm
Shape of screw head	Cross slotted
Colour tint	Metal

Complementary

Quantity per set	Set of 100
Sale per indivisible quantity	100

Environment

Material	Cavity fixing: zinc electroplated Screw: steel
Practical load capacity	Shear: 270 N Pull-out load: 80 N
Thickness	0...12 mm fixture
Ambient air temperature for operation	-40...80 °C
Diameter	4.5 mm
Length	35 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.4 cm
Package 1 Width	1.4 cm
Package 1 Length	5.5 cm
Package 1 Weight	6 g
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	5.8 cm
Package 2 Width	12.3 cm
Package 2 Length	16 cm
Package 2 Weight	676 g
Unit Type of Package 3	CAR
Number of Units in Package 3	2400

Package 3 Height	25.4 cm
Package 3 Width	18.3 cm
Package 3 Length	76.5 cm
Package 3 Weight	16.71 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------