

Product data sheet

Characteristics

1220104

Thorsman - TPD - cavity fixing - with screw - set of 100



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Product name	Thorsman TPD
Device short name	TPD
Provided equipment	Screw
Mounting support	Board material
Device application	Board material
Mounting support	Wall mounted
Screw diameter	4.5 mm
Screw length	35 mm
Size of screw head	8 mm
Shape of screw head	Cross slotted
Colour tint	Metal

Complementary

Quantity per set	Set of 100
Sale per indivisible quantity	100

Environment

Material	Cavity fixing: zinc electroplated Screw: steel
Practical load capacity	Shear: 270 N Pull-out load: 80 N
Thickness	0...12 mm fixture
Ambient air temperature for operation	-40...80 °C
Diameter	4.5 mm
Length	35 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2 g
Package 1 Height	1.3 cm
Package 1 width	1.3 cm
Package 1 Length	3.7 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------