

Product data sheet

Characteristics

1220S25

Screwed Conduit, Clipsal - Cable Management, 25mm, Brass Plug

Main

Product brand	Clipsal
Range of product	Series 1220S



Complementary

Material	Brass
Product destination	Diameter: 25 mm tube
Stub stiffness	Rigid

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	2.5 cm
Package 1 Length	2.5 cm
Package 1 Weight	36 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	6 cm
Package 2 Width	7.8 cm
Package 2 Length	7.8 cm
Package 2 Weight	780 g
Unit Type of Package 3	CAR
Number of Units in Package 3	240
Package 3 Height	17.5 cm
Package 3 Width	16 cm
Package 3 Length	24 cm
Package 3 Weight	8.9 kg

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
