

Product data sheet

Characteristics

1220S32

Clipsal - Cable Management, Series 1220S Brass Plugs, 32mm, Screwed Conduit, Brass Plug



Main

Product brand	Clipsal
Range of product	Series 1220S

Complementary

Material	Brass
Product destination	Diameter: 32 mm tube
Stub stiffness	Rigid

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.025 cm
Package 1 Width	3.2 cm
Package 1 Length	3.2 cm
Package 1 Weight	0.06 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6 cm
Package 2 Width	7.8 cm
Package 2 Length	7.8 cm
Package 2 Weight	0.6 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	17 cm
Package 3 Width	28.2 cm
Package 3 Length	30 cm
Package 3 Weight	15 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations