

## Product data sheet

### Characteristics

# 1220S40

Clipsal - Cable Management, Series 1220S  
Brass Plugs, 40mm, Screwed Conduit, Brass  
Plug



### Main

Product brand	Clipsal
Range of product	Series 1220S






### Complementary

Material	Brass
Product destination	Diameter: 40 mm tube
Stub stiffness	Rigid

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.025 cm
Package 1 Width	4 cm
Package 1 Length	4 cm
Package 1 Weight	0.096 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6 cm
Package 2 Width	7.8 cm
Package 2 Length	7.8 cm
Package 2 Weight	0.994 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	17 cm
Package 3 Width	28.2 cm
Package 3 Length	30 cm
Package 3 Weight	25 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations