

Product data sheet

Characteristics

1220S40

Screwed Conduit, Clipsal - Cable Management, 40mm, Brass Plug



Main

Product brand	Clipsal
Range of product	Series 1220S

Complementary

Material	Brass
Product destination	Diameter: 40 mm tube
Stub stiffness	Rigid

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.025 cm
Package 1 Width	4 cm
Package 1 Length	4 cm
Package 1 Weight	0.096 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6 cm
Package 2 Width	7.8 cm
Package 2 Length	7.8 cm
Package 2 Weight	0.994 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	17 cm
Package 3 Width	28.2 cm
Package 3 Length	30 cm
Package 3 Weight	25 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations