

## Product data sheet

### Characteristics

# 1235/25

## Cable Management Machined Brass, 1 Inch Male to 25mm Female Brass Adaptor



### Main

Product brand	Clipsal
---------------	---------



### Complementary

Material	Brass
Connector type	Thread connector
Product destination	Diameter: 25 mm tube
Length	40 mm

### Environment

Standards	AS 2052 AS 1721 AS 1722.2 ASC 66.1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.025 cm
Package 1 Width	2.877 cm
Package 1 Length	2.877 cm
Package 1 Weight	0.056 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	7 cm
Package 2 Width	10.7 cm
Package 2 Length	14 cm
Package 2 Weight	1.182 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	22.6 cm
Package 3 Width	19.1 cm
Package 3 Length	35.9 cm
Package 3 Weight	12 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>