

Product data sheet

Characteristics

1235PG16

Brass Adaptor, Clipsal - Cable Management,
PG16 Male to 20mm Female



Main

Product brand	Clipsal
---------------	---------

Complementary

Material	Brass
Connector type	Thread connector
Product destination	Diameter: 20 mm tube
Length	33 mm

Environment

Standards	DIN 40430 AS 1721 AS 2052
-----------	---------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.325 cm
Package 1 Width	2.401 cm
Package 1 Length	2.401 cm
Package 1 Weight	36 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	9.4 cm
Package 2 Width	10.7 cm
Package 2 Length	14 cm
Package 2 Weight	1.9 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations