

## Product data sheet

### Characteristics

# 1242AC25

## Conduit Coupling, Clipsal - Cable Management, Brass, M25x1.5 x 1-16, Female to Female



### Main

Product brand	Clipsal
---------------	---------

### Complementary

Material	Brass
Connector type	Thread connector
Product destination	Diameter: 25 mm tube
Length	34 mm

### Environment

Standards	AS 1721 ASC 66.1 AS 2052 AS 1722.2
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.425 cm
Package 1 Width	3.035 cm
Package 1 Length	3.035 cm
Package 1 Weight	0.07 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

