

## Product data sheet

### Characteristics

# 1242BSP20/25

## Coupling, Clipsal - Cable Management, Machined Brass, 3/4 in BSP Female to 25mm Female



### Main

Product brand	Clipsal
---------------	---------

### Complementary

Material	Brass
Connector type	Thread connector
Product destination	Diameter: 20 mm tube Diameter: 25 mm tube
Length	35 mm



### Environment

Standards	AS 1721 CS 792/S BS 2779 AS 1722.2 AS 2052
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.525 cm
Package 1 Width	3.02 cm
Package 1 Length	3.02 cm
Package 1 Weight	0.064 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 <a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations