

Product data sheet

Characteristics

1242BU20

Clipsal - Cable Management, Machined Brass, Unions, 20mm Brass Barrel Union



Main

Product brand	Clipsal
---------------	---------

Complementary

Material	Brass
Connector type	Thread connector
Product destination	Diameter: 33 mm tube
Length	37.5 mm

Environment

Standards	AS 1721 AS 2052 CS 792/S
-----------	--------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.75 cm
Package 1 Width	3.3 cm
Package 1 Length	3.3 cm
Package 1 Weight	0.086 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	9.6 cm
Package 2 Width	16.8 cm
Package 2 Length	17.8 cm
Package 2 Weight	4.3 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	20 cm
Package 3 Width	18 cm
Package 3 Length	22 cm
Package 3 Weight	8.6 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations