

Product data sheet

Characteristics

1242BU25

Clipsal - Cable Management, Machined Brass, Unions, 25mm Brass Barrel Union



Main

Product brand	Clipsal
---------------	---------

Complementary

Material	Brass
Connector type	Thread connector
Product destination	Diameter: 38 mm tube
Length	40 mm

Environment

Standards	AS 1721 AS 2052 CS 792/S
-----------	--------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	3.8 cm
Package 1 Length	3.8 cm
Package 1 Weight	0.112 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	10.2 cm
Package 2 Width	12 cm
Package 2 Length	17 cm
Package 2 Weight	2.32 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	25 cm
Package 3 Width	21.4 cm
Package 3 Length	33.8 cm
Package 3 Weight	11.6 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations