

## Product data sheet

### Characteristics

# 1242BUS20

## Clipsal - Cable Management, Machined Brass, Unions, 20mm Steel Barrel Union



### Main

Product brand	Clipsal
---------------	---------

### Complementary

Material	Steel
Surface treatment	Zinc plated
Connector type	Thread connector
Product destination	Diameter: 33 mm tube
Length	36.5 mm

### Environment

Standards	AS 1721 AS 2052 CS 792/S
-----------	--------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.65 cm
Package 1 Width	3.3 cm
Package 1 Length	3.3 cm
Package 1 Weight	0.082 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	9.6 cm
Package 2 Width	16.8 cm
Package 2 Length	17.8 cm
Package 2 Weight	4.15 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	20 cm
Package 3 Width	18 cm
Package 3 Length	22 cm
Package 3 Weight	8.5 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations