

Product data sheet

Characteristics

1242S20

Clipsal - Cable Management, Machined Brass, 20mm Steel Coupling, Zinc Plated



Main

Product brand	Clipsal
---------------	---------



Complementary

Material	Steel
Surface treatment	Zinc plated
Surface finish	Polished
Connector type	Thread connector
Product destination	Diameter: 20 mm tube
Length	30 mm

Environment

Standards	CS 792/S AS 2052 AS 1721
-----------	--------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	2.5 cm
Package 1 Length	2.5 cm
Package 1 Weight	21 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	11 cm
Package 2 Width	12.6 cm
Package 2 Length	17.4 cm
Package 2 Weight	1.142 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	25 cm
Package 3 Width	21.4 cm
Package 3 Length	33.8 cm
Package 3 Weight	250 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile