

## Product data sheet

### Characteristics

# 1242S25

## COUPLING STEEL CON 25MM Z/PL



### Main

Product brand	Clipsal
---------------	---------

### Complementary

Material	Steel
Surface treatment	Zinc plated
Surface finish	Polished
Connector type	Thread connector
Product destination	Diameter: 25 mm tube
Length	35.5 mm

### Environment

Standards	CS 792/S AS 2052 AS 1721
-----------	--------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	65.1 g
Package 1 Height	3.7 cm
Package 1 width	3.1 cm
Package 1 Length	3.1 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Weight	3.344 kg
Package 2 Height	11.4 cm
Package 2 width	13.8 cm
Package 2 Length	17.6 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	7 kg
Package 3 Height	20 cm
Package 3 width	18 cm
Package 3 Length	22 cm

## Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>