

Product data sheet

Characteristics

1242S25

Cable Management Machined Brass, 25mm Steel Coupling, Zinc Plated



Main

Product brand	Clipsal
---------------	---------



Complementary

Material	Steel
Surface treatment	Zinc plated
Surface finish	Polished
Connector type	Thread connector
Product destination	Diameter: 25 mm tube
Length	35.5 mm

Environment

Standards	CS 792/S AS 2052 AS 1721
-----------	--------------------------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	3.1 cm
Package 1 Length	3.1 cm
Package 1 Weight	65.1 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	50
Package 2 Height	11.4 cm
Package 2 Width	13.8 cm
Package 2 Length	17.6 cm
Package 2 Weight	3.344 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	20 cm
Package 3 Width	18 cm
Package 3 Length	22 cm
Package 3 Weight	7 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile