

Product data sheet

Characteristics

1242S40

COUPLING STEEL CON 40MM Z/PL



Main

Product brand	Clipsal
---------------	---------

Complementary

Material	Steel
Surface treatment	Cast galvanised
Surface finish	Polished
Connector type	Thread connector
Product destination	Diameter: 40 mm tube
Length	48.5 mm

Environment

Standards	CS 792/S AS 2052 AS 1721
-----------	--------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	311.0 g
Package 1 Height	5.5 cm
Package 1 width	5 cm
Package 1 Length	5.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	3.11 kg
Package 2 Height	110 mm
Package 2 width	124 mm
Package 2 Length	170 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	30
Package 3 Weight	9.33 kg
Package 3 Height	117 mm
Package 3 width	250 mm
Package 3 Length	310 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile