

## Product data sheet

### Characteristics

# 1244/32

## ELBOW INSP GALV COND 32MM



### Main

Product brand	Clipsal
Range of product	Series 1244

### Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	32 mm
Connector type	Thread connector
Operating angle	90 °
Length	79 mm
Inner radius	10 mm




### Environment

Standards	AS 2052 AS 1721
-----------	--------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	418 g
Package 1 Height	4.5 cm
Package 1 width	6 cm
Package 1 Length	11 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	4.358 kg
Package 2 Height	11.2 cm
Package 2 width	17.2 cm
Package 2 Length	18.2 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	20
Package 3 Weight	8.36 kg
Package 3 Height	20 cm
Package 3 width	18 cm
Package 3 Length	22 cm

## Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration