

Product data sheet

Characteristics

1244/32

Clipsal - Cable Management, Inspection Elbows, 32mm Galvanised Cast Iron



Main

Product brand	Clipsal
Range of product	Series 1244

Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	32 mm
Connector type	Thread connector
Operating angle	90 °
Length	79 mm
Inner radius	10 mm






Environment

Standards	AS 2052 AS 1721
-----------	--------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	6 cm
Package 1 Length	11 cm
Package 1 Weight	418 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	11.2 cm
Package 2 Width	17.2 cm
Package 2 Length	18.2 cm
Package 2 Weight	4.358 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	20
Package 3 Height	20 cm
Package 3 Width	18 cm
Package 3 Length	22 cm
Package 3 Weight	8.36 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations