

Product data sheet

Characteristics

1244/40

Clipsal - Cable Management, Inspection Elbows, 40mm Galvanised Cast Iron



Main

| | |
|------------------|-------------|
| Product brand | Clipsal |
| Range of product | Series 1244 |

Complementary

| | |
|-------------------|------------------|
| Material | Cast iron |
| Surface treatment | Galvanised |
| Diameter | 40 mm |
| Connector type | Thread connector |
| Operating angle | 90 ° |
| Length | 95 mm |
| Inner radius | 13 mm |

Environment

| | |
|-----------|--------------------|
| Standards | AS 1721 AS 2052 |
|-----------|--------------------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.6 cm |
| Package 1 Width | 9.2 cm |
| Package 1 Length | 9.2 cm |
| Package 1 Weight | 0.614 kg |

Offer Sustainability

| | |
|--------------------------|--|
| Sustainable offer status | Green Premium product |
| RECh Regulation | RECh Declaration |
| RECh free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
