

Product data sheet

Characteristics

1244/50

ELBOW INSP GALV COND 50MM



Main

Product brand	Clipsal
Range of product	Series 1244

Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	50 mm
Connector type	Thread connector
Operating angle	90 °
Length	116 mm
Inner radius	25 mm

Environment

Standards	AS 1721 AS 2052
-----------	--------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	920 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	4.6 kg
Package 2 Height	10.6 cm
Package 2 width	18 cm
Package 2 Length	25.7 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	10
Package 3 Weight	9.2 kg
Package 3 Height	22.6 cm
Package 3 width	19.1 cm
Package 3 Length	35.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile