

## Product data sheet

### Characteristics

# 1244003

## Thorsman - TSP-10xM5 - cavity fixing - with screw - set of 25



### Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TSP
Provided equipment	Screw
Mounting support	Board material - thickness: 3...20 mm
Device application	3...20 mm board material
Mounting support	Wall mounted
Thread type	M5
Screw diameter	5 mm
Screw length	50 mm
Drilling diameter	10 mm
Colour tint	Blue/white

### Complementary

Quantity per set	Set of 25
Net weight	0.00896 kg

### Environment

Material	Screw: steel electroplated Collar: PA (polyamide) Spring: PA (polyamide)
Practical load capacity	Shear: 250 N for 13 mm board 4.5) Pull-out load: 75 N for 13 mm board 6)
Thickness	0...12 mm fixture 13 mm board
Environmental characteristic	Corrosion resistance
Ambient air temperature for operation	-40...80 °C
Diameter	20 mm
Length	54 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	9 g
Package 1 Height	1 cm
Package 1 width	1 cm
Package 1 Length	6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	25
Package 2 Weight	250 g
Package 2 Height	5.8 cm
Package 2 width	8 cm
Package 2 Length	12.2 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------