

Product data sheet

Characteristics

1244003

Thorsman installation material, TSP-10xM5, cavity fixing, with screw, set of 25



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TSP
Provided equipment	Screw
Mounting support	Board material - thickness: 3...20 mm
Device application	3...20 mm board material
Mounting support	Wall mounted
Thread type	M5
Screw diameter	5 mm
Screw length	50 mm
Drilling diameter	10 mm
Colour tint	Blue/white

Complementary

Quantity per set	Set of 25
Net weight	0.00896 kg

Environment

Material	Screw: steel electroplated Collar: PA (polyamide) Spring: PA (polyamide)
Practical load capacity	Shear: 250 N for 13 mm board 4.5) Pull-out load: 75 N for 13 mm board 6)
Thickness	0...12 mm fixture 13 mm board
Environmental characteristic	Corrosion resistance
Ambient air temperature for operation	-40...80 °C
Diameter	20 mm
Length	54 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	1.0 cm
Package 1 Length	6.0 cm
Package 1 Weight	9.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	25
Package 2 Height	5.8 cm
Package 2 Width	8.0 cm
Package 2 Length	12.2 cm
Package 2 Weight	250.0 g
Unit Type of Package 3	BB2

Number of Units in Package 3	250
Package 3 Height	12.0 cm
Package 3 Width	15.4 cm
Package 3 Length	32.4 cm
Package 3 Weight	2.534 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------