

Product data sheet

Characteristics

1245/20

Clipsal - Cable Management, Solid Elbows, 20mm Galvanised Cast Iron



Main

Product brand	Clipsal
Range of product	Series 1245

Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	20 mm
Connector type	Thread connector
Operating angle	90 °
Length	56 mm
Inner radius	7 mm






Environment

Standards	AS 1721 AS 2052
-----------	--------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	2.9 cm
Package 1 Length	8 cm
Package 1 Weight	138 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	9.6 cm
Package 2 Width	16.8 cm
Package 2 Length	17.8 cm
Package 2 Weight	3 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	4800
Package 3 Weight	720 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations