

## Product data sheet

### Characteristics

# 1245/20

## ELBOW SOLID GALV COND 20MM



### Main

|                  |             |
|------------------|-------------|
| Product brand    | Clipsal     |
| Range of product | Series 1245 |

### Complementary

|                   |                  |
|-------------------|------------------|
| Material          | Cast iron        |
| Surface treatment | Galvanised       |
| Diameter          | 20 mm            |
| Connector type    | Thread connector |
| Operating angle   | 90 °             |
| Length            | 56 mm            |
| Inner radius      | 7 mm             |

### Environment

|           |                    |
|-----------|--------------------|
| Standards | AS 1721<br>AS 2052 |
|-----------|--------------------|

### Packing Units

|                  |        |
|------------------|--------|
| Package 1 Weight | 138 g  |
| Package 2 Weight | 3 kg   |
| Package 3 Weight | 720 kg |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| RECh Regulation            | <a href="#">REACH Declaration</a>  |
| RECh free of SVHC          | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |