

## Product data sheet

### Characteristics

# 1245/25

## ELBOW SOLID GALV COND 25MM



### Main

Product brand	Clipsal
Range of product	Series 1245

### Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	25 mm
Connector type	Thread connector
Operating angle	90 °
Length	68 mm
Inner radius	12 mm

### Environment

Standards	AS 2052 AS 1721
-----------	--------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	368 g
Package 1 Height	33 mm
Package 1 width	60 mm
Package 1 Length	145 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	3.68 kg
Package 2 Height	100 mm
Package 2 width	170 mm
Package 2 Length	180 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	50 kg
Package 3 Height	190 mm
Package 3 width	203 mm
Package 3 Length	175 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>