

Product data sheet

Characteristics

1245/25

Clipsal - Cable Management, Solid Elbows, 25mm Galvanised Cast Iron



Main

Product brand	Clipsal
Range of product	Series 1245

Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	25 mm
Connector type	Thread connector
Operating angle	90 °
Length	68 mm
Inner radius	12 mm

Environment

Standards	AS 2052 AS 1721
-----------	--------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	6 cm
Package 1 Length	14.5 cm
Package 1 Weight	368 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	10 cm
Package 2 Width	17 cm
Package 2 Length	18 cm
Package 2 Weight	3.68 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	19 cm
Package 3 Width	20.3 cm
Package 3 Length	17.5 cm
Package 3 Weight	50 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile