

## Product data sheet

### Characteristics

# 1245/40

## ELBOW SOLID GALV COND 40MM



### Main

Product brand	Clipsal
Range of product	Series 1245

### Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	40 mm
Connector type	Thread connector
Operating angle	90 °
Length	95 mm
Inner radius	25 mm

### Environment

Standards	AS 2052 AS 1721
-----------	--------------------

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Weight	0.096 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>