

## Product data sheet

### Characteristics

# 1245/50

## ELBOW SOLID GALV COND 50MM



### Main

Product brand	Clipsal
Range of product	Series 1245

### Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	50 mm
Connector type	Thread connector
Operating angle	90 °
Length	118 mm
Inner radius	25 mm

### Environment

Standards	AS 1721 AS 2052
-----------	--------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.88 kg
Package 1 Height	11.8 cm
Package 1 width	5 cm
Package 1 Length	5 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	17.6 kg
Package 2 Height	26.5 cm
Package 2 width	24.6 cm
Package 2 Length	40.2 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	4.4 kg
Package 3 Height	10.6 cm
Package 3 width	18 cm
Package 3 Length	25.7 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>