

# Product data sheet

## Characteristics

# 1247/40

## BEND SOLID GALV COND 40MM



### Main

Product brand	Clipsal
Range of product	Series 247

### Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	40 mm
Connector type	Thread connector
Operating angle	90 °
Length	182 mm
Inner radius	105 mm

### Environment

Standards	AS 2052 AS 1721
-----------	--------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1031 g
Package 1 Height	47 mm
Package 1 width	47 mm
Package 1 Length	255 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	5.155 kg
Package 2 Height	110 mm
Package 2 width	255 mm
Package 2 Length	310 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	10
Package 3 Weight	10.31 kg
Package 3 Height	265 mm
Package 3 width	246 mm
Package 3 Length	402 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>