

Product data sheet

Characteristics

1259B25

LOCKNUT BRASS HEX COND 25MM



Main

Range	Clipsal
Product or component type	Lock nut
Accessory / separate part category	Fixing accessory
Material	Brass




Complementary

Diameter	External: 37 mm Thread: 25 mm
Height pitch dimension	1.5 mm
Threaded length	32 mm
Thickness	5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16 g
Package 1 Height	5 mm
Package 1 width	30 mm
Package 1 Length	34 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Weight	0.824 kg
Package 2 Height	68 mm
Package 2 width	96 mm
Package 2 Length	134 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	8.5 kg
Package 3 Height	132 mm
Package 3 width	200 mm
Package 3 Length	395 mm

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration