

Product data sheet

Characteristics

1259B25

LOCKNUT BRASS HEX COND 25MM



Main

Range	Clipsal
Product or component type	Lock nut
Accessory / separate part category	Fixing accessory
Range compatibility	Clipsal
Material	Brass

Complementary

Diameter	External: 37 mm Thread: 25 mm
Height pitch dimension	1.5 mm
Threaded length	32 mm
Thickness	5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.5 cm
Package 1 Width	3 cm
Package 1 Length	3.4 cm
Package 1 Weight	16 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	6.8 cm
Package 2 Width	9.6 cm
Package 2 Length	13.4 cm
Package 2 Weight	824 g
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Height	13.2 cm
Package 3 Width	20 cm
Package 3 Length	39.5 cm
Package 3 Weight	8.5 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile