

## Product data sheet

### Characteristics

# 1259B63

## LOCKNUT BRASS HEX COND 63MM



### Main

Range	Clipsal
Product or component type	Lock nut
Accessory / separate part category	Fixing accessory
Range compatibility	Clipsal
Material	Brass






### Complementary

Diameter	Thread: 63 mm External: 83 mm
Height pitch dimension	1.5 mm
Threaded length	75 mm
Thickness	8.5 mm

### Packing Units

Package 1 Weight	0.136 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 <a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.