

Product data sheet

Characteristics

1259S25

Clipsal - Cable Management, Machined Brass, Steel Couplings, 25mm Steel Locknut



Main

Range	Clipsal
Product or component type	Lock nut
Accessory / separate part category	Fixing accessory
Range compatibility	Clipsal
Material	Steel

Complementary

Diameter	Thread: 25 mm External: 43 mm
Height pitch dimension	1.5 mm
Threaded length	37 mm
Thickness	4 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.5 cm
Package 1 Width	3.3 cm
Package 1 Length	3.3 cm
Package 1 Weight	14 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations