

## Product data sheet

### Characteristics

# 1259S40

## Machined Brass, Clipsal - Cable Management, Steel Couplings, 40mm Steel Locknut



### Main

Range	Clipsal
Product or component type	Lock nut
Accessory / separate part category	Fixing accessory
Range compatibility	Clipsal
Material	Steel




### Complementary

Diameter	Thread: 40 mm External: 60 mm
Height pitch dimension	1.5 mm
Threaded length	52 mm
Thickness	5 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.5 cm
Package 1 Width	6 cm
Package 1 Length	6 cm
Package 1 Weight	40 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	7.8 cm
Package 2 Width	11.8 cm
Package 2 Length	15.8 cm
Package 2 Weight	850 g

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

---