

Product data sheet

Characteristics

1260025

Thorsman - TMX-8xM4 - cavity fixing - with threaded screw - set of 100



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TMX
Provided equipment	Threaded screw
Mounting support	High load installation in board material - thickness: 5...15 mm
Device application	5...15 mm high load installation in board material
Mounting support	Wall mounted
Thread type	M4
Screw diameter	4 mm
Screw length	40 mm
Shape of screw head	Cross slotted Combi-head
Screwdriver shape	Philips
Drilling diameter	8 mm
Colour tint	Grey Metal

Complementary

Quantity per set	Set of 100
Net weight	0.0072 kg

Environment

Material	Screw: steel electroplated Cavity fixing: sheet metal electroplated
Practical load capacity	Shear: 200 N 2.5) Pull-out load: 140 N 3)
Thickness	0...18 mm fixture
Environmental characteristic	Fire resistance
Ambient air temperature for operation	-40...80 °C
Diameter	14 mm
Length	47 mm

Packing Units

Package 1 Weight	7.200 g
Package 1 Height	14.000 mm
Package 1 width	14.000 mm
Package 1 Length	47.000 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------